

# C2207

## C2207

### Dri-Can® Reusable Desiccant Container

- Protects many applications from rust, corrosion, mold, mildew and other damage caused by moisture or high humidity.
- Reusable - regenerates in a microwave or conventional oven. To recharge in microwave, set to high, stand the canister on its end, microwave canister for 3 minutes. Repeat until silica gel is blue. To recharge in oven, set to 300° and heat canister for 3 hours or until silica gel is blue.
- Can be used to dry the air in all types of moisture resistant containers and packages, including glass jars, air-tight cans, plastic pouches, tool boxes, wall safes, display cases, and more.
- Indicating silica gel changes from blue to pink in colour to let you know when Dri-Can canister regeneration is needed.

