



Determine an Object's Surface Temperature without Physical Contact

Overview

The SI-111-PW, manufactured by Apogee, is a version of our SI-111 that is fitted with a connector for attachment to a prewired enclosure. This precision infrared radiometer determines the surface temperature of an object without

physical contact. The SI-111-PW measures both the subject's surface temperature and the sensor-body temperature. A Campbell Scientific data logger uses these measurements to calculate the correct temperature of the subject.

Benefits and Features

- › Cable connects directly with a prewired enclosure
- › Compatible with most Campbell Scientific data loggers
- › Measures surface temperature continuously in the field
- › Provides road surface, plant canopy, soil surface, snow surface, and water surface temperature measurements
- › Avoids influencing the temperature, providing more accurate measurements
- › Ideal for providing spatial averages
- › Rugged construction—two temperature probes housed in an aluminum body with a germanium window

Detailed Description

The SI-111-PW consists of a thermopile, which measures surface temperature, and a thermistor, which measures sensor body temperature. The two temperature sensors are housed in a rugged aluminum body that contains a germanium window.

Both the thermopile and the thermistor output a millivolt signal that most of our data loggers can measure. The data logger uses the Stefan-Boltzman equation to correct for the effect of sensor body temperature on the target temperature.

The corrected readings yield an absolute accuracy of $\pm 0.2^{\circ}\text{C}$ from -10° to $+65^{\circ}\text{C}$.

Field of View (FOV)

The SI-111-PW has a 22-degree half-angle field of view (FOV). The FOV is reported as the half-angle of the apex of the cone formed by the target (cone base) and the detector (cone apex). The target is a circle from which 98% of the radiation viewed by the detector is being emitted.

Specifications

Input Power	2.5 V excitation (for thermistor)
Response Time	< 1 s (to changes in target temperature)
Target Temperature Output Signal	60 μ V per $^{\circ}$ C difference from sensor body
Body Temperature Output Signal	0 to 2500 mV
Optics	Germanium lens
Wavelength Range	8 to 14 μ m (corresponds to atmospheric window)
Field of View (FOV)	22 $^{\circ}$ half angle
Operating Temperature Range	-55 $^{\circ}$ to +80 $^{\circ}$ C

Operating Relative Humidity Range	0 to 100% RH
Cable Description	4.5 m (14.76 ft) twisted, shielded 4-conductor wire with Santoprene casing, ending in pigtails
Absolute Accuracy	› \pm 0.5 $^{\circ}$ C (-40 $^{\circ}$ to +70 $^{\circ}$ C) › \pm 0.2 $^{\circ}$ C (-10 $^{\circ}$ to +65 $^{\circ}$ C)
Uniformity	› \pm 0.3 $^{\circ}$ C (-40 $^{\circ}$ to +70 $^{\circ}$ C) › \pm 0.1 $^{\circ}$ C (-10 $^{\circ}$ to +65 $^{\circ}$ C)
Repeatability	› \pm 0.1 $^{\circ}$ C (-40 $^{\circ}$ to +70 $^{\circ}$ C) › \pm 0.05 $^{\circ}$ C (-10 $^{\circ}$ to +65 $^{\circ}$ C)
Diameter	2.3 cm (0.9 in.)
Length	6 cm (2.4 in.)
Weight	190 g (6.7 oz)

For comprehensive details, visit: www.campbellsci.com/si-111-pw 



Campbell Scientific, Inc. | 815 W 1800 N | Logan, UT 84321-1784 | (435) 227-9120 | www.campbellsci.com
AUSTRALIA | BRAZIL | CANADA | CHINA | COSTA RICA | FRANCE | GERMANY | THAILAND | SOUTH AFRICA | SPAIN | UK | [USA](#)

© 2019 Campbell Scientific, Inc. | 08/16/2019